

| Average Face Velocity | | 300 | 400 | 500 | 600 | 700 |
|------------------------------|-----|------|------|------|------|------|
| ETB900/ETB900 INS | | | | | | |
| 22 x 22 | CFM | 725 | 970 | 1210 | 1450 | 1695 |
| Ak 2.420 | -Ps | .004 | .006 | .010 | .014 | .020 |
| 46 x 22 | CFM | 1520 | 2024 | 2530 | 3035 | 3540 |
| Ak 5.060 | -Ps | .003 | .006 | .010 | .012 | .018 |
| ETB280 | | | | | | |
| 22 x 22 | CFM | 785 | 1045 | 1305 | 1565 | 1825 |
| Ak 2.610 | -Ps | .015 | .030 | .043 | .062 | .084 |
| 46 x 22 | CFM | 1635 | 2180 | 2725 | 3270 | 3815 |
| Ak 5.460 | -Ps | .015 | .030 | .040 | .059 | .081 |
| ETB900FF/ETB900FF INS | | | | | | |
| 20 x 20 | CFM | 600 | 800 | 1000 | 1200 | 1400 |
| Ak 2.000 | -Ps | .003 | .006 | .010 | .014 | .019 |
| 44 x 20 | CFM | 1320 | 1760 | 2200 | 2640 | 3080 |
| Ak 4.400 | -Ps | .003 | .006 | .009 | .013 | .018 |
| RZ-Egg Crate | | | | | | |
| 20 x 20 | CFM | 420 | 560 | 700 | 840 | 980 |
| Ak 1.400 | -Ps | .004 | .008 | .013 | .018 | .025 |

Note: Tested without filters. Typical capacity is 2 CFM per square inch of nominal filter area. Recommended face velocity is 300-450 FPM. Velocities higher will decrease filter performance, increase flow resistance, and possibly be of noise concern. Velocity measured 1" from face.